# Aluminum AlSi10Mg



Several materials with a wide range of applications for e-manufacturing are available for the EOSINT M-systems. EOS Aluminum AISi 10Mg is an aluminum alloy in fine powder form that has been specially optimized for EOSINT M 270-systems (Titanium Version). Other materials are also available for EOSINT M-systems and new materials are developed continuously. The related material data sheets contain information provided for the system requirements.



## **DESCRIPTION, APPLICATION**

EOS Aluminum AISi 10Mg is a master alloy aluminum-powder. AISi 10Mg is a typical casting alloy with god casting properties and is used for cast parts with thin walls and complex geometry. The alloy combination silicon/magnesium results in a significant increase in the strength and hardness. It also features good dynamic properties and is therefore used for parts subject to high loads. Standard building parameters completely melt the powder in the entire part. Parts made of EOS Aluminum AISi 10Mg can be machined, wire eroded and electrical discharge machined, welded, micro-blasted, polished and coated. Unexposed powder can be re-used.

Typical applications:

- -Direct manufacture of functional prototypes, small production runs, user-specific products or spare parts.
- -Parts that require a combination of good thermal properties with low weight, e.g. for motorsport applications.

## THERMAL PROPERTIES OF THE PARTS

The information relates to the usage of materials with the EOSINT M 270-systems in accordance with the actual specification (including the latest release of the process software PSW and, if necessary, hardware specified for the related material) and as per the operating instructions. All values stated are approximate. If not otherwise stated, the mechanical and physical properties refer to standard parameters and specimen parts built in the horizontal direction. They are dependent on the building parameters and building strategies used and can be varied by the operator to suit the application. The information corresponds to the latest findings. The information is not intended to assure specific properties of the product or suitability for a specific application. EOS, EOSINT, DMLS, DirectTool and DirectPart are registered trademarks of EOS GmbH.

## **TECHNICAL DATA**

### GENERAL PROCESS AND GEOMETRICAL DATA

Recommended minimum layer thickness	30um
	1.2mil
Smallest wall thickness [1]	0.3-0.4 mm
	11.8-15.8 mil



Surface roughness, as built	Ra– um, Rz- um
	Ra-Rz-mil
Volume rate with standard parameters (full density) [2]	4.8 mm3/s
	1.1 in3/h

[1] Mechanical stability dependent on the geometry (wall height etc.) and application

[2] The volume rate is a measure of the building speed during laser exposure. The overall building speed is dependent on the average volume rate, the time required for coating (depending on the number of layers) and other factors, e.g. DMLS settings.

#### PHYSICAL AND CHEMICAL PROPERTIES OF THE PARTS

Material composition	Si (9.0-11.0 %)
	Fe max 0.55 %
	Cu max 0.05 %
	Mn max ).45 %
	Mg (0.2-0.45 %)
	Ni max 0.05 %
	Zn max 0.10%
	Pb max 0.05 %
	Sn max 0.05 %
	Ti max 0.15 %
	All rest
Relative density with standard parameters	approx 100 %
Density with standard parameters	2.68 g/cm3
	0.97 lb/in3

	As Built	Heat treated T6 [5]
Tensile Strength		
-in horizontal direction (XY)	± MPa	±MPa



-in vertical direction (Z)	340±40 MPa	315±20 MPa
Yield Point (Rp 0.2 %)		
-in horizontal direction (XY)	250±15 MPa	260±15 MPa
-in vertical direction (Z)	±MPa	±MPa
Elongation at tear		
-in horizontal direction (XY)	% ± %	%±%
-in vertical direction (Z)	1.5 % ± 0.5 %	1.2 ± 0.5 %
Hardness [4]	120 ±5 HBW	112 ± 5 HBW
Fatigue strength [6]		
-in vertical direction (Z)	97 ± 7 MPa	93 ± 3 MPa

[3] Mechanical strength tested as per ISO 6892:1998(E) annex C, proportional specimens, specimen diameter 5mm, initial measured length 25mm, specimens manufactured with 30 um layers.

[4] Hardness test in accordance with Brinell (HBW 2.5/62/5) as per DIN En ISO 6506-1.

[5] Heat Treatment T6: solution annealing xH/530 C, quenching in water bath, elevated temperature age hardening Yh/160 C

[6] Fatigue test with test frequency of 50Hz, R= -1, measurement stopped on reaching 5 million cycles without fracture.

About Proto3000

Proto3000 connects companies and individuals to the digital tools they need in order to achieve greater capability, scalability, and efficiency. We are a company rooted in providing solutions, and through the development of our product and service portfolio, we are committed to finding the one that is right for you. Having worked with thousands of companies, from various industries, we have gained an understanding of the digital demands required in research and development, product development, and manufacturing. Our suite of solutions have been carefully selected to ensure that you can meet these demands, while positioning your business for sustainable growth and a competitive advantage.

Our business operates in four international market segments; Product Development, Manufacturing, Engineering, and Dentistry. Our solutions include rapid prototyping, 3D printing, engineering design, laser scanning and digital dental products and services.

